

# TruAir Scope Drying Cabinets

**Model Numbers:** SAS-4P-HA, SAS-8P-HA (Half Width)  
SAS-9P-HA, SAS-18P-HA (Full Width)

**Color:** Bright White

**Cabinet Filter Efficiency:** Removes 99.97% of Particles (up to 0.3µm)

**Capacity:** 4, 8, 9, or 18 Flexible Large Diameter Endoscopes

**Ext. Dimensions:** 93-3/4"H X 21-5/8"W X 18-3/4"D (Half Width)  
93-3/4"H X 40-7/8"W X 18-3/4"D (Full Width)


**Construction:** Powder Coated Metal  
Padded Lower Back Wall (Distal Tip Protection)

**Air Supply:** Hospital Air Integration (Please refer to the Hospital Air Integration document)  
HEPA Filter Fan (Cabinet)


**Electrical Supply:** 120 V Wall Plug-3 A (8' Cord Exiting Top Right of Cabinet)

**Options:** Door Activated LED Lighting  
Keyless Lock  
Temperature and Humidity Gauge

## Features




SAS-4P-HA, SAS-8P-HA Half Width TruAir Scope Drying Cabinet



SAS-9P-HA, SAS-18P-HA Full Width TruAir Scope Drying Cabinet

# TruAir Scope Drying Cabinets


## Measurements



POWDER-COATED METAL CABINET  
 SAS-4P-HA Capsa METAL SCOPE CABINET  
 Locking Overlay Hinged Doors with Glass Inserts & Sloped Top, Holds 4 Flexible Endoscopes

# TruAir Scope Drying Cabinets


## Measurements



POWDER-COATED METAL CABINET  
 SAS-8P-HA Capsa METAL SCOPE CABINET  
 Locking Overlay Hinged Doors with Glass Inserts & Sloped Top, Holds 8 Flexible Endoscopes

# TruAir Scope Drying Cabinets


## Measurements



POWDER-COATED METAL CABINET  
 SAS-9P-HA Capsa METAL SCOPE CABINET  
 Locking Overlay Hinged Doors with Glass Inserts & Sloped Top, Holds 9 Flexible Endoscopes

# TruAir Scope Drying Cabinets

## Measurements



POWDER-COATED METAL CABINET  
 SAS-18P-HA Capsa METAL SCOPE CABINET  
 Locking Overlay Hinged Doors with Glass Inserts & Sloped Top, Holds 18 Flexible Endoscopes